



This Datasheet is a valuable resource for the hardware appliance of Power IQ. It breaks down each feature into smaller parts, listing the key features and specifications to help gain a better knowledge and understanding of the hardware.

Features	E2
<b>Form Factor</b>	2U
<b>Dimensions</b>	33" X 13" X 24"
<b>Weight</b>	62 lbs
<b>Operating Temperature</b>	10°C - 35°C (50°F - 95°F)
<b>Processor</b>	Intel® Xeon® processor E5-2650 v2 Quantity: 2 2.6 GHz 8-core 16 threads 20 MB cache
<b>Memory</b>	Quantity: 4 Processor: 1866 MHz / PC3 14900 Memory Size: 16GB
<b>Network Interface</b>	Serial Port: 2 serial COM port (1 rear & 1 header) Network Controllers: Intel® i350 Dual Port Gigabit Ethernet, 10BASE-T, 100BASE-TX, and 1000BASE-T, RJ45 output ,1x PHY (dedicated IPMI)
<b>Hard Disk &amp; Controller</b>	Units: 2 Capacity: 600GB Cache: 16MB Interface: SAS 6.0 Gbps Number of heads: 8 Rotational Speed 15700 rpm
<b>DVD</b>	Internal SATA/300

Contact [tech@sunbirdcim.com](mailto:tech@sunbirdcim.com) if you have any questions. Contact your reseller or [customerquestions@sunbirdcim.com](mailto:customerquestions@sunbirdcim.com) to buy the E2 appliance.

July 24, 2015

Sunbird® is a registered trademark of Sunbird Software. All others are registered trademarks or trademarks of their respective owners.

This note is intended for Sunbird customers only; its use, in whole or part, for any other purpose without the express written permission from Sunbird Software is prohibited.

© 2015 Sunbird Software All rights reserved.